

Uddeholm QRO 90 Supreme/QRO 90 HT Stock Standard

QRO 90 SUPREME

Flat bar

Soft annealed/Unmachined

Soft annealed/Machined

mm	43	50	54	63,5	76,2	90	102	115	127	153	178	203
153				<input checked="" type="checkbox"/>								
158			<input type="checkbox"/>									
203				<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>							
210	<input type="checkbox"/>		<input type="checkbox"/>									
254				<input checked="" type="checkbox"/>						<input checked="" type="checkbox"/>		
300		<input checked="" type="checkbox"/>										
305				<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>		<input checked="" type="checkbox"/>		<input checked="" type="checkbox"/>	
407								<input checked="" type="checkbox"/>				<input checked="" type="checkbox"/>
620							<input checked="" type="checkbox"/>					

Round bar

Soft annealed/Machined ●

Soft annealed/Unmachined ○

mm	16	20	22	25,4	28	30	32	35	41	43	45
	○	○	○	○	○	○	○	○	○	○	○

mm	50,8	55	60	63,5	70	76,2	80	90	100	105	110	115	120	127	140	153	160	180
	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●

mm	190	203	210	216	225	230	246	254	260	280	305	320	330	356	407	457	500
	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●

The stock standard might change without notice

Issue date
March 2009
1 (2)

Uddeholm QRO 90 Supreme/QRO 90 HT Stock Standard

QRO 90 HT

Round bar

Prehardened 37-41 HRC/Unmachined

mm	6	8	10	12,7	16	18	20	22	25,4	30	35	41
	○	○	○	○	○	○	○	○	○	○	○	○