

## Uddeholm QRO 90 Supreme/QRO 90 HT Stock Standard

### QRO 90 SUPREME

#### Flat bar

Soft annealed/Unmachined ☐

Soft annealed/Machined ▬

mm	43	50	54	63,5	76,2	90	102	115	127	140	153	178	191	203
153				▬										
158			☐											
203				▬	▬									▬
210			☐						▬					
254										▬	▬			
305				▬	▬	▬	▬	▬	▬	▬		▬	▬	
407								▬						▬
620							▬							

#### Round bar

Soft annealed/Machined ●

Soft annealed/Unmachined ○

mm	16	20	22	25,4	28	30	32	35	41	43	45
	○	○	○	○	○	○	○	○	○	○	○

mm	50,8	55	60	63,5	70	76,2	80	90	100	105	110	115	120	127	140	153	160	180
	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●

mm	190	203	210	225	230	246	254	260	280	305	320	330	356	407
	●	●	●	●	●	●	●	●	●	●	●	●	●	●

The stock standard might change without notice

Issue date  
Dec, 2017  
1 (2)

## Uddeholm QRO 90 Supreme/QRO 90 HT Stock Standard

### QRO 90 HT

#### Round bar

Prehardened 37-41 HRC/Unmachined

mm	6	8	10	12,7	16	18	20	22	25,4	30	35	41
	○	○	○	○	○	○	○	○	○	○	○	○